

Reliable

Approved materials acc. to FDA and EC 1935/2004

Cost effective

Continuous coating is ensured thanks to maintenance-free operation

User friendly


Simple mounting

Drum coater storage tank

Level measurement and point level detection in the storage tank of a drum coater

In the pharmaceutical industry, tablets are coated with colouring agents or active ingredients in a drum coater. This coating in the form of a liquid suspension, contains colouring or solids and is stored in a storage tank next to the drum. It is sprayed into the drum via nozzles for even distribution on the surface of the tablets. Reliable level measurement in the storage tank is required to ensure that there is always enough of the liquid suspension for tablet coating. Overflow and dry run protection is provided by a reliable level switch.

[More details](#)



VEGAPOINT 21

Capacitive level switch as overflow and dry run protection in a supply tank

- Simple operation, including optical switching display
- Reliable switching point, non-sensitive to buildup
- Compact design ideally suited for tight spaces

[Show Product](#)



VEGAPULS 6X

Non-contact level measurement with radar in a storage tank

- Reliable and accurate measurement even in small tanks
- Approved materials according to FDA and EC 1935/2004 ensure hygienic storage of the suspension
- Direct measured value display on the sensor and via Bluetooth for easy visualization of the container contents

[Show Product](#)

BASIC

PRO

VEGAPOINT 21

[Show Product](#)

VEGAPULS 6X

[Show Product](#)**Measuring range - Distance**

-

Measuring range - Distance

120 m

Process temperature

-40 ... 115 °C

Process temperature

-196 ... 450 °C

Process pressure

-1 ... 64 bar

Process pressure

-1 ... 160 bar

Materials, wetted parts316L
PEEK**Accuracy**

± 1 mm

Threaded connection

≥ G½, ≥ ½ NPT

Frequency6 GHz
26 GHz
80 GHz**Hygienic fittings**Clamp ≥ 2", DN50 - DIN32676, ISO2852
Clamp ≥ 1" - DIN32676, ISO2852
Clamp ≥ 1½" - DIN32676, ISO2852
Slotted nut ≥ 1½", ≥ DN40 - DIN 11851
Slotted nut ≥ DN25 - DIN 11851
Slotted nut ≥ DN32 - DIN 11851**Beam angle**

≥ 3°

Seal materialEPDM
FKM**Materials, wetted parts**PTFE
PVDF
316L
PP
PEEK**Protection rating**IP66/IP67
IP69**Threaded connection**

≥ G¾, ≥ ¾ NPT

OutputTransistor (NPN/PNP)
IO-Link**Flange connection**

≥ DN20, ≥ ¾"

Ambient temperature

-40 ... 70 °C

Hygienic fittingsClamp ≥ 1½" - DIN32676, ISO2852
Slotted nut ≥ 2", DN50 - DIN 11851
Varivent ≥ DN25
hygienic fitting with tension flange DN32
hygienic fitting F40 with compression nut
Hygienic screw connections ≥ DN50 tube ø53 -
DIN11864-1-A
Hygienic flange connection ≥ DN50 DIN11864-2
Hygienic clamp connection ≥ DN50 pipe Ø53 - DIN11864-
3-A
DRD connection ø 65 mm
SMS 1145 DN51