

Reliable

Reliable operation despite extreme process conditions

Cost effective

Measuring system can be installed without invasive work on the vessel wall and insulation

User friendly

Simple retro installation



Digester

Level detection and pressure measurement in the digester

In the digester, the action of chemical dissolution removes the lignin binder, thereby exposing and freeing the cellulose fibres. During the cooking process according to the alkaline sulphate method, the fibres are fed into the digester by means of steam pressure. To enable fully automatic operation of the digester, a point level detection of the filling is required. The vessel pressure also needs to be carefully monitored throughout this process.

More details



POINTRAC 31

Radiation-based detection of maximum level for controlling the filling process

- Enables automated operation of the digester
- Non-contact measurement right through the vessel wall
- Maintenance-free operation

Show Product

VEGABAR 81

Pressure transmitter for pressure measurement in the digester

- · Pressure measurement in aggressive media and high temperatures
- Long-term chemical resistance
- Resistant to pressure surges during emptying

Show Product



PRO	PRO
POINTRAC 31 Show Product	VEGABAR 81 Show Product
Measuring range - Distance -	Measuring range - Distance -
Process temperature -40 60 °C	Measuring range - Pressure -1 1000 bar
Process pressure -	Process temperature -90 400 °C
Vaterials, wetted parts No wetted material	Process pressure -1 1000 bar
Seal material no media contact	Accuracy 0.2 % 0.1 %
Housing material Aluminium Stainless steel (precision casting)	Materials, wetted parts Alloy C22 (2.4602)
Protection rating IP66/IP67	Alloy 400 (2.4360) Tantalum Alloy C276 (2.4819)
Dutput Profibus PA Foundation Fieldbus 8/16 mA/HART - four-wire	Duplex (1.4462) Titanium Grade 2 (3.7035) 1.4435 316/316L Titanium Grade 7 (3.7235)
Ambient temperature -40 60 °C	Threaded connection ≥ G½, ≥ ½ NPT
	Flange connection ≥ DN25, ≥ 1"

Flange connection ≥ DN25, ≥ 1" Hygenic fittings Clamp ≥ 1" - DIN32676, ISO2852 Slotted nut ≥ 1½", ≥ DN40 - DIN 11851 hygienic fitting with tension flange DN32 hygienic fitting F40 with compression nut Hygienic fittings ≥ DN40 - DIN11864-1-A Seal material no media contact

