

Agitating tank

#### Reliable

Reliable measurement, unaffected by media properties

### Cost effective

Long service life ensures uninterrupted operation for extended periods

### **User friendly**

Non-contact measurement through glass





More details

# VEGAPULS 6X

Non-contact level measurement with radar in agitating tanks for raw and intermediate products

Level measurement and point level detection in an agitating tank

continuous production, reliable level measurement and point level detection are essential.

In the pharmaceutical industry, numerous liquids with widely different properties are required. Liquid

intermediate products must be made available and held ready for further processes. To ensure smooth,

- Reliable measurement through inspection glass, independent of medium
- · Wide dynamic range allows measurement even with slightly slanted windows
- Instrument ensures consistently reliable measurement, unaffected by temperature fluctuations and gas phases

### **Show Product**

## **VEGASWING 63**

Point level detection with vibrating level switches in agitating tanks for raw and intermediate products

- Level detector for all liquid media, regardless of viscosity
- Thanks to the exact switching point, the entire container capacity can be utilized and efficient production ensured despite changing media
- Simple setup and commissioning

### **Show Product**



VEGAPULS 6X Show Product	VEGASWING 63 Show Product
Measuring range - Distance 120 m	Process temperature -50 250 °C
Process temperature -196 450 °C	Process pressure -1 64 bar
Process pressure -1 160 bar	Version Standard Hygienic applications
Accuracy ± 1 mm	with gas-tight leadthrough with tube extension with temperature adapter
Frequency 6 GHz 26 GHz 80 GHz	Materials, wetted parts PFA 316L
Beam angle ≥ 3°	Alloy C22 (2.4602) Alloy 400 (2.4360) ECTFE Enamel
Materials, wetted parts PTFE PVDF 316L	Threaded connection ≥ G <sup>3</sup> 4, ≥ <sup>3</sup> 4 NPT
PP PEEK	Flange connection ≥ DN25, ≥ 1"
Threaded connection ≥ G¾, ≥ ⅔ NPT	Hygenic fittings Clamp ≥ 1" - DIN32676, ISO2852
Flange connection ≥ DN20, ≥ ¾"	Slotted nut ≥ 1½", ≥ DN40 - DIN 11851   Varivent ≥ DN25   hygienic fitting F40 with compression nut
Hygenic fittings Clamp ≥ $1\frac{1}{2}$ " - DIN32676, ISO2852 Slotted nut ≥ 2", DN50 - DIN 11851 Varivent ≥ DN25 hygienic fitting with tension flange DN32 hygienic fitting F40 with compression nut	SMS 1145 DN51 SMS DN38 Hygienic fittings ≥ DN25 - DIN11864-1-A Hygienic flange connection DIN11864-2-A; DN60(ISO)ø60,3 SMS socket piece DN38 PN6
Hygienic screw connections ≥ DN50 tube ø53 - DIN11864-1-A	Seal material no media contact
Hygienice flange connection ≥ DN50 DIN11864-2 Hygienic clamp connection ≥ DN50 pipe Ø53 - DIN11864- 3-A DRD connection Ø 65 mm SMS 1145 DN51	Housing material Plastic Aluminium Stainless steel (precision casting)

IP66/IP67 IP66/IP68 (1 bar) IP65

