

### Reliable

Reliable measurement even with strong dust generation

### Cost effective

Optimum storage capacity utilization

### **User friendly**

Maintenance and wear-free

# 0 0 0

# Blending bed

### Level measurement of the blending bed

To attain high quality and uniform material consistency in the finished cement, the raw material is homogenized in a so-called blending bed. The rock is distributed evenly over the blending bed with a stacker. Material is removed with a scraper. To ensure that the incoming material is distributed as evenly as possible, the level must be continuously measured.

### More details



### **VEGAPULS 6X**

Level measurement with radar in the blending bed

- Precise measurement through good focusing
- High measurement certainty, even with intense dust and noise generation
- Maintenance-free operation thanks to encapsulated antenna system

### **Show Product**



## **VEGAPULS 6X**

### **Show Product**



### Measuring range - Distance

120 m

### Process temperature

-196 ... 450 °C

### Process pressure

-1 ... 160 bar

### Accuracy

± 1 mm

### Frequency

6 GHz

26 GHz

80 GHz

### Beam angle

≥ 3°

### Materials, wetted parts

PTFE

PVDF

316L PP

PEEK

### Threaded connection

≥ G¾, ≥ ¾ NPT

### Flange connection

≥ DN20, ≥ ¾"

### Hygenic fittings

Clamp ≥ 1½" - DIN32676, ISO2852

Slotted nut ≥ 2", DN50 - DIN 11851

Varivent ≥ DN25

hygienic fitting with tension flange DN32

hygienic fitting F40 with compression nut

Hygienic screw connections  $\geq$  DN50 tube ø53 -

DIN11864-1-A

Hygienice flange connection ≥ DN50 DIN11864-2

Hygienic clamp connection ≥ DN50 pipe Ø53 - DIN11864-

3-A

DRD connection ø 65 mm

SMS 1145 DN51

